## PRACTICAL DIGITAL SOLUTIONS

Unitron Hearing's complete range of hearing solutions takes full advantage of digital technology to address the real, everyday problems of hearing loss and hearing aids.

<ul> <li>Conversa – the highly advanced solution to your clients' top concerns: feedback, telephone use, occlusion and understanding conversation in noise.</li> <li>16 independent channels of compression</li> <li>Realtime feedback canceller reacts within milliseconds to provide precise and adaptive cancellation</li> <li>ClearCall eliminates the need for a telecoil for telephone and cell phone use</li> <li>ClearPath<sup>™</sup> Technology, three sophisticated technologies working together to optimize speech intelligibility and listening comfort: <ul> <li>Intelligent noise reduction enhances speech while reducing annoying background noise</li> <li>Vector directional microphone standard on BTE, optional for full-shell, half-shell and canal</li> <li>ClearPath processing strategy applies the appropriate scheme for every input level; quiet mode expansion, linear, WDRC, compression limiting</li> <li>Up to three programs for different listening environments</li> <li>Start up mute</li> <li>CIC to full-shell, BTE and Power BTE</li> </ul> </li> </ul>	
Heleon A start for the second bar the second bar the	
<b>Unison 4</b> – the fully featured, accessible digital solution.	
<ul> <li>4 independent channels of compression</li> <li>4 processing chaines to tailer to eligit processing</li> </ul>	
<ul> <li>4 processing choices to tailor to client needs</li> <li>Digital WDRC<sup>4</sup></li> </ul>	
ASP Noise Suppression	
Adaptive Compression	
Linear Limiting	
<ul> <li>Vector directional microphone standard on BTE, optional on full-shell, half-shell and canal</li> </ul>	
Quiet Mode Expansion for improved sound quality in quiet environments	
Static feedback manager	
Up to 3 programs for different listening environments	
<ul> <li>CIC to full-shell, BTE and Power BTE</li> </ul>	
<b>Unison 2</b> – simplified for first-time clients and previous analog wearers.	
2 independent channels of compression	
Digital WDRC with Linear capabilities	
Vector directional microphone standard on BTE, optional on full-shell, half-shell and canal	
Quiet Mode Expansion for improved sound quality in quiet environments	
Static feedback manager	
2 programs for different listening environments	
CIC to full-shell, BTE and Power BTE	
<b>Unison 2 Single Memory</b> – digital hearing aid at conventional price.	
<ul> <li>2 independent channels of compression</li> </ul>	
▶ Digital WDRC with Linear capabilities	
Quiet Mode Expansion for improved sound quality in quiet environments	
Static feedback manager	

CIC to full-shell, BTE and Power BTE

## A refreshingly practical approach to hearing solutions. Easy to select. Easy to fit.



www.unitronhearing.com